

**SICK**

### PBS-RP2K0SN1SS0CMA0G

Inombolo yendawo: PBS-RP2K0SN1SS0CMA0G  
 Umkhiqizi / Umshicileli: SICK  
 Ingcaciso yeMveliso: SEN PRESS 0-2000 PSI  
 Maxwebhu:  
 Umkhumbi: ehong Kong  
 Indlela yokuthunyelwa: DHL/Fedex/TNT/UPS/EMS

**ISICELO**

**SESIKATSHULWA**

Umfanekiso ungasakaliswa. Bona iinkcukacha zeenkukacha zeemveliso.

#### Iinkcukacha zePBS-RP2K0SN1SS0CMA0G

INOMBOLO YENDAWO	PBS-RP2K0SN1SS0CMA0G
UMENZI	SICK
INKCAZO	SEN PRESS 0-2000 PSI
ISIMO SOBUME BENKOKELI / ISIMO SEROHS	
ISHITI YEDATHA	
UKUNIKEZELA NGEEVOTSI	15 V ~ 35 V
STYLE TERMINATION	Connector
IPHAKHEJI YECANDELO LENKONZO	-
UCHUNGECHUNGE	-
UHLOBO LOXINZELELO	Gauge
PORT STYLE	Threaded
UBUKHULU BEPORT	Female - 1/4" (6.35mm) NPT
IPHAKHEJI / IIMEKO	Module
UHLOBO LOHLOBO	Analog Voltage, PNP
ISIPHUMO	0 V ~ 10 V
AMANYE AMAGAMA	6050827
UKUSHISA OKUSEBENZAYO	-20°C ~ 85°C
U XINZELELO	1999.9 PSI (13789 kPa)
UXINZELELO OLUNINZI	-
IXESHA LENKQUBO YENKOKELI YEHLABATHI	3 Weeks
IIMBONAKALO	-
INKCAZO ECACILEYO	Pressure Sensor 1999.9 PSI (13789 kPa) Gauge Female - 1/4" (6.35mm) NPT 0 V ~ 10 V Module
UKUCHANEKA	±1%

#### Amanqaku afanayo

SICK PBS-RP2K0SN1SS0CMA0G	Umhambisi we-PBS-RP2K0SN1SS0CMA0G	Umboneleli we-PBS-RP2K0SN1SS0CMA0G
Ixabiso le-PBS-RP2K0SN1SS0CMA0G	Imifanekiso ye-PBS-RP2K0SN1SS0CMA0G	Umfanekiso we-PBS-RP2K0SN1SS0CMA0G
Idatha ye-PBS-RP2K0SN1SS0CMA0G yePD	I-PBS-RP2K0SN1SS0CMA0G Khuphela iDatasheet	Idatha ye-PBS-RP2K0SN1SS0CMA0G
Ivenkile ye-PBS-RP2K0SN1SS0CMA0G	Thenga iPBS-RP2K0SN1SS0CMA0G	Thenga iSICK PBS-RP2K0SN1SS0CMA0G
SICK PBS-RP2K0SN1SS0CMA0G	Umboneleli we-SICK	Umhambisi we-SICK
SICK PBS-RP2K0SN1SS0CMA0G		

#### Iimveliso ezihambelanayo

<p><b>PBS-RP300SG1SSNAMA0Z</b>                  Abavelisi: SICK                  Inkcazo: SEN PRESS 0-300 PSI                  Ikhona evenkileni: Out stock</p> <p style="text-align: center; background-color: #cccccc; padding: 2px;"><b>RFQ</b></p>	<p><b>PBS-RP300SN1SS0AMA0Z</b>                  Abavelisi: SICK                  Inkcazo: SEN PRESS 0-300 PSI                  Ikhona evenkileni: Out stock</p> <p style="text-align: center; background-color: #cccccc; padding: 2px;"><b>RFQ</b></p>
<p><b>PBS-RP300SN1SS0D5A0Z</b>                  Abavelisi: SICK                  Inkcazo: SEN PRESS 0-300 PSI                  Ikhona evenkileni: Out stock</p> <p style="text-align: center; background-color: #cccccc; padding: 2px;"><b>RFQ</b></p>	<p><b>PBS-RP2K0SN1SS0Q5A0Z</b>                  Abavelisi: SICK                  Inkcazo: SEN PRESS 0-2000 PSI                  Ikhona evenkileni: Out stock</p> <p style="text-align: center; background-color: #cccccc; padding: 2px;"><b>RFQ</b></p>
<p><b>PBS-RP200SN1SS0Q5A0Z</b>                  Abavelisi: SICK                  Inkcazo: SEN PRESS 0-200 PSI                  Ikhona evenkileni: Out stock</p> <p style="text-align: center; background-color: #cccccc; padding: 2px;"><b>RFQ</b></p>	<p><b>PBS-RP300SN1SS0BMA0Z</b>                  Abavelisi: SICK                  Inkcazo: SEN PRESS 0-300 PSI                  Ikhona evenkileni: Out stock</p> <p style="text-align: center; background-color: #cccccc; padding: 2px;"><b>RFQ</b></p>
<p><b>PBS-RP2K0SN1SS0E5A0Z</b>                  Abavelisi: SICK                  Inkcazo: SEN PRESS 0-2000 PSI                  Ikhona evenkileni: Out stock</p> <p style="text-align: center; background-color: #cccccc; padding: 2px;"><b>RFQ</b></p>	<p><b>PBS-RP200SG2SS0D5A0Z</b>                  Abavelisi: SICK                  Inkcazo: SEN PRESS 0-200 PSI                  Ikhona evenkileni: Out stock</p> <p style="text-align: center; background-color: #cccccc; padding: 2px;"><b>RFQ</b></p>
<p><b>PBS-RP1K5SN1SS0AMA0Z</b>                  Abavelisi: SICK                  Inkcazo: SEN PRESS 0-1500 PSI                  Ikhona evenkileni: Out stock</p> <p style="text-align: center; background-color: #cccccc; padding: 2px;"><b>RFQ</b></p>	<p><b>PBS-RP1K5SN1SS0BMA0Z</b>                  Abavelisi: SICK                  Inkcazo: SEN PRESS 0-1500 PSI                  Ikhona evenkileni: Out stock</p> <p style="text-align: center; background-color: #cccccc; padding: 2px;"><b>RFQ</b></p>
<p><b>PBS-RP200SN1SS0FMA0Z</b>                  Abavelisi: SICK                  Inkcazo: SEN PRESS 0-200 PSI                  Ikhona evenkileni: Out stock</p> <p style="text-align: center; background-color: #cccccc; padding: 2px;"><b>RFQ</b></p>	<p><b>PBS-RP1K5SN1SS0D5A0Z</b>                  Abavelisi: SICK                  Inkcazo: SEN PRESS 0-1500 PSI                  Ikhona evenkileni: Out stock</p> <p style="text-align: center; background-color: #cccccc; padding: 2px;"><b>RFQ</b></p>