



Advanced Photonix (Luna)

### PDB-C137F

Inombolo yendawo:  
 Umkhiqizi / Umshicileli:  
 Ingcaciso yeMveliso  
 Maxwebhu:  
 RoHS Imeko  
 Umkhumbi  
 Indlela yokuthunyelwa

PDB-C137F  
 Advanced Photonix (Luna Optoelectronics)  
 PHOTODIODE BLUE W/DF 5MM T1 3/4  
 PDB-C137F.pdf  
 Iqukethe i-lead / RoHS engahambelaniyo  
 ehong Kong  
 DHL/Fedex/TNT/UPS/EMS

#### Optoelectronics



Umfanekiso ungunakaliswa. Bona iinkcukacha zeenkukacha zeemveliso.

ISICELO

SESIKATSHULWA

#### Iinkcukacha zePDB-C137F

|                                       |   |
|---------------------------------------|---|
| INOMBOLO YENDAWO                      | PDB-C137F   |
| UMENZI                                | Advanced Photonix (Luna Optoelectronics)            |
| INKCAZO                               | PHOTODIODE BLUE W/DF 5MM T1 3/4                     |
| ISIMO SOBUME BENKOKELI / ISIMO SEROHS | Iqukethe i-lead / RoHS engahambelaniyo              |
| ISHITI YEDATHA                        | PDB-C137F.pdf                                       |
| WAVELENGTH                            | 950nm   |
| I-VOLTAGE - DC IJIKA (VR) (MAX)       | 50V   |
| UKUJONGA I-ANGLE                      | 40°   |
| RECTECTRAL RANGE                      | 700nm ~ 1100nm                                      |
| UCHUNGECHUNGE                         | -   |
| UXANDUVA @ NM                         | -   |
| IXESHA LOKUPHENDULA                   | 10ns  |
| PACKAGING                             | Bulk  |
| IPHAKHEJI / IIMEKO                    | Radial, 5mm Dia (T 1 3/4)                           |
| AMANYE AMAGAMA                        | PT-PDB-C137F  |
| UKUSHISA OKUSEBENZAYO                 | -40°C ~ 80°C  |
| UHLOBO LOKUPHAKAMISA                  | Through Hole  |
| INQANABA LOKUSONDEZA UBUNINZI (MSL)   | 1 (Unlimited)                                       |
| ISIMO SOBUME BENKOKELI / ISIMO SEROHS | Contains lead / RoHS non-compliant                  |
| UHLOBO LWEDIODE                       | PIN   |
| INKCAZO ECACILEYO                     | Photodiode 950nm 10ns 40° Radial, 5mm Dia (T 1 3/4) |
| OKWANGOKU - OMNYAMA (TYP)             | 2nA   |
| UMBALA - UPHUCULWE                    | Blue  |
| INDAWO ESEBENZAYO                     | 0.74mm <sup>2</sup>                                 |

#### Amanqaku afanayo

|  |  |  |
|--|--|--|
| Advanced Photonix (Luna Optoelectronics) PDB-C137F | Umhambisi we-PDB-C137F                                 | Umboneleli we-PDB-C137F                                    |
| Ixabiso le-PDB-C137F                               | Imifanekiso ye-PDB-C137F                               | Umfanekiso we-PDB-C137F                                    |
| Idatha ye-PDB-C137F yePD                           | I-PDB-C137F Khuphela iDatasheet                        | Idatha ye-PDB-C137F  |
| Ivenkile ye-PDB-C137F                              | Thenga iPDB-C137F                                      | Thenga iAdvanced Photonix (Luna Optoelectronics) PDB-C137F |
| Advanced Photonix (Luna Optoelectronics) PDB-C137F | Umboneleli we-Advanced Photonix (Luna Optoelectronics) | Umhambisi we-Advanced Photonix (Luna Optoelectronics)      |
| Advanced Photonix (Luna Optoelectronics) PDB-C137F | Advanced Photonix Inc PDB-C137F                        | Advanced Photonix (Luna Optoelectronics) PDB-C137F         |
| Luna Optoelectronics PDB-C137F                     |  |  |

#### Iimveliso ezihambelanayo

|   |   |
|---|---|
| <br><b>PDB-C135</b><br>Abavelisi: Advanced Photonix (Luna Optoelectronics)<br>Inkcazo: PHOTODIODE BLUE 5MM T1 3/4<br>Ikhona evenkileni: Out stock<br>       | <br><b>PDB-C136F</b><br>Abavelisi: Advanced Photonix (Luna Optoelectronics)<br>Inkcazo: PHOTODIODE BLUE W/DF 5MM T1 3/4<br>Ikhona evenkileni: Out stock<br> |
| <br><b>PDB-C139F</b><br>Abavelisi: Advanced Photonix (Luna Optoelectronics)<br>Inkcazo: PHOTODIODE BLUE W/DF 5MM T1 3/4<br>Ikhona evenkileni: Out stock<br> | <br><b>PDB-C136</b><br>Abavelisi: Advanced Photonix (Luna Optoelectronics)<br>Inkcazo: PHOTODIODE BLUE 5MM T1 3/4<br>Ikhona evenkileni: Out stock<br>       |
| <br><b>PDB-C140</b><br>Abavelisi: Advanced Photonix (Luna Optoelectronics)<br>Inkcazo: PHOTODIODE BLUE 29.02MM SQ CER<br>Ikhona evenkileni: Out stock<br>   | <br><b>PDB-C135F</b><br>Abavelisi: Advanced Photonix (Luna Optoelectronics)<br>Inkcazo: PHOTODIODE BLUE W/DF 5MM T1 3/4<br>Ikhona evenkileni: Out stock<br> |
| <br><b>PDB-C142</b><br>Abavelisi: Advanced Photonix (Luna Optoelectronics)<br>Inkcazo: PHOTODIODE BLUE 5MM T1 3/4<br>Ikhona evenkileni: Out stock<br>       | <br><b>PDB-C138F</b><br>Abavelisi: Advanced Photonix (Luna Optoelectronics)<br>Inkcazo: PHOTODIODE BLUE W/DF 5MM T1 3/4<br>Ikhona evenkileni: Out stock<br> |
| <br><b>PDB-C139</b><br>Abavelisi: Advanced Photonix (Luna Optoelectronics)<br>Inkcazo: PHOTODIODE BLUE 5MM T1 3/4<br>Ikhona evenkileni: Out stock<br>       | <br><b>PDB-C138</b><br>Abavelisi: Advanced Photonix (Luna Optoelectronics)<br>Inkcazo: PHOTODIODE BLUE 5MM T1 3/4<br>Ikhona evenkileni: Out stock<br>       |
| <br><b>PDB-C134F</b><br>Abavelisi: Advanced Photonix (Luna Optoelectronics)<br>Inkcazo: PHOTODIODE BLUE W/DF 1.55MM T1<br>Ikhona evenkileni: 17 pcs<br>     | <br><b>PDB-C137</b><br>Abavelisi: Advanced Photonix (Luna Optoelectronics)<br>Inkcazo: PHOTODIODE BLUE 5MM T1 3/4<br>Ikhona evenkileni: Out stock<br>       |

