



Omron Automation & Safety

## A22NZ-BPA-NGA

Inombolo yendawo:  
 Umkhqizi / Umshicileli:  
 Ingcaciso yeMveliso  
 Maxwebhu:  
 RoHS Imeko  
 Umkhumbi  
 Indlela yokuthunyelwa

A22NZ-BPA-NGA  
 Omron Automation & Safety  
 CONFIG SW BODY PUSHBUT NON-ILLUM  
[PDF A22NZ-BPA-NGA.pdf](#)  
 Ukukhokela mahala / RoHS Ukuthobela  
 ehong Kong  
 DHL/Fedex/TNT/UPS/EMS



ISICELO

SESIKATSHULWA

Umfanekiso ungabonakaliswa. Bona iinkcukacha zeenkukacha zeemveliso.

### Iinkcukacha zeA22NZ-BPA-NGA

|  |  |
|--|--|
| INOMBOLO YENDAWO   | A22NZ-BPA-NGA  |
| UMENZI   | Omron Automation & Safety                                  |
| INKCAZO  | CONFIG SW BODY PUSHBUT NON-ILLUM                           |
| ISIMO SOBUME BENKOKELI / ISIMO SEROHS                              | Ukukhokela mahala / RoHS Ukuthobela                        |
| ISHITI YEDATHA   | <a href="#">PDF A22NZ-BPA-NGA.pdf</a>                      |
| UHLOBO   | Maintained   |
| UCHUNGECHUNGE  | A22NN  |
| KU FUNEKA  | Contact Block(s)   |
| I-PANEL CUTOUT UBUKHULU  | 22.3mm (Round)   |
| AMANYE AMAGAMA   | A22NZBPANGA  |
| INQANABA LOKUSONDEZA UBUNINZI (MSL)                                | 1 (Unlimited)  |
| IXESHA LENKQUBO YENKOKELI YEHLABATHI                               | 2 Weeks  |
| ISIMO SOBUME BENKOKELI / ISIMO SEROHS                              | Lead free / RoHS Compliant                                 |
| UKUKHANYA  | Non-Illuminated  |
| INKCAZO ECACILEYO  | Configurable Switch Body Pushbutton, Round Non-Illuminated |
| UHLOBO LWE-ACTUATOR  | Pushbutton, Round  |
| (KHETHA OKOKUQALA, EMVA KOKO UFAKE IIFAYILE) ULUHLU OLUHAMBELANAYO | Omron, A22NN   |

### Amanqaku afanayo

|   |   |   |
|---|---|---|
| Omron Automation & Safety A22NZ-BPA-NGA | Umhambisi we-A22NZ-BPA-NGA                | Umboneleli we-A22NZ-BPA-NGA                     |
| Ixabiso le-A22NZ-BPA-NGA                | Imifanekiso ye-A22NZ-BPA-NGA              | Umfanekiso we-A22NZ-BPA-NGA                     |
| Idatha ye-A22NZ-BPA-NGA yePD            | I-A22NZ-BPA-NGA Khuphela iDatasheet       | Idatha ye-A22NZ-BPA-NGA                         |
| Ivenkile ye-A22NZ-BPA-NGA               | Thenga iA22NZ-BPA-NGA                     | Thenga iOmron Automation & Safety A22NZ-BPA-NGA |
| Omron Automation & Safety A22NZ-BPA-NGA | Umboneleli we-Omron Automation & Safety   | Umhambisi we-Omron Automation & Safety          |
| Omron Automation & Safety A22NZ-BPA-NGA | Omron Automation and Safety A22NZ-BPA-NGA |   |

### Iimveliso ezihambelanayo

|   |   |
|---|---|
| <p><b>A22NZ-BPA-NBA</b><br/>                 Abavelisi: Omron Automation &amp; Safety<br/>                 Inkcazo: CONFIG SW BODY PUSHBUT NON-ILLUM<br/>                 Ikhona evenkileni: Out stock<br/> <a href="#">RFQ</a></p> | <p><b>A22NZ-BPA-TOA</b><br/>                 Abavelisi: Omron Automation &amp; Safety<br/>                 Inkcazo: CONFIG SW BODY PUSHBUTTON ILLUM<br/>                 Ikhona evenkileni: Out stock<br/> <a href="#">RFQ</a></p>  |
| <p><b>A22NZ-BPA-TGA</b><br/>                 Abavelisi: Omron Automation &amp; Safety<br/>                 Inkcazo: CONFIG SW BODY PUSHBUTTON ILLUM<br/>                 Ikhona evenkileni: Out stock<br/> <a href="#">RFQ</a></p>  | <p><b>A22NZ-BNM-UOA</b><br/>                 Abavelisi: Omron Automation &amp; Safety<br/>                 Inkcazo: CONFIG SW BODY PUSHBUT NON-ILLUM<br/>                 Ikhona evenkileni: Out stock<br/> <a href="#">RFQ</a></p> |
| <p><b>A22NZ-BNM-URA</b><br/>                 Abavelisi: Omron Automation &amp; Safety<br/>                 Inkcazo: CONFIG SW BODY PUSHBUT NON-ILLUM<br/>                 Ikhona evenkileni: 20 pcs<br/> <a href="#">RFQ</a></p>    | <p><b>A22NZ-BPA-NWA</b><br/>                 Abavelisi: Omron Automation &amp; Safety<br/>                 Inkcazo: CONFIG SW BODY PUSHBUT NON-ILLUM<br/>                 Ikhona evenkileni: 19 pcs<br/> <a href="#">RFQ</a></p>    |
| <p><b>A22NZ-BPA-NRA</b><br/>                 Abavelisi: Omron Automation &amp; Safety<br/>                 Inkcazo: CONFIG SW BODY PUSHBUT NON-ILLUM<br/>                 Ikhona evenkileni: Out stock<br/> <a href="#">RFQ</a></p> | <p><b>A22NZ-BNM-UYA</b><br/>                 Abavelisi: Omron Automation &amp; Safety<br/>                 Inkcazo: CONFIG SW BODY PUSHBUT NON-ILLUM<br/>                 Ikhona evenkileni: Out stock<br/> <a href="#">RFQ</a></p> |
| <p><b>A22NZ-BPA-NAA</b><br/>                 Abavelisi: Omron Automation &amp; Safety<br/>                 Inkcazo: CONFIG SW BODY PUSHBUT NON-ILLUM<br/>                 Ikhona evenkileni: Out stock<br/> <a href="#">RFQ</a></p> | <p><b>A22NZ-BPA-TAA</b><br/>                 Abavelisi: Omron Automation &amp; Safety<br/>                 Inkcazo: CONFIG SW BODY PUSHBUTTON ILLUM<br/>                 Ikhona evenkileni: Out stock<br/> <a href="#">RFQ</a></p>  |
| <p><b>A22NZ-BPA-NYA</b><br/>                 Abavelisi: Omron Automation &amp; Safety<br/>                 Inkcazo: CONFIG SW BODY PUSHBUT NON-ILLUM<br/>                 Ikhona evenkileni: Out stock<br/> <a href="#">RFQ</a></p> | <p><b>A22NZ-BNM-UWA</b><br/>                 Abavelisi: Omron Automation &amp; Safety<br/>                 Inkcazo: CONFIG SW BODY PUSHBUT NON-ILLUM<br/>                 Ikhona evenkileni: Out stock<br/> <a href="#">RFQ</a></p> |

**Ilungelo lokushicilela © 2020 Umthengisi othembekileyo wezinto ze-Elektroniki- Ocean-Components.com**

I-imeyile: I-Info@Ocean-Components.com

Idilesi: Room 2102, Connaught Commercial Building, 185 Wan Chai Rd, Wan Chai, Hong Kong

